


# PEX Connecting Solutions

## Benefits

- One tool for all sizes
- 360° Stepless design
- Certified by NSF to meet NSF / ANSI 14 requirements
- Fast, simple and secure installation



## SEALING SOLUTIONS



### Standard PEX Series

- Provides a 360° leak-free seal
- Narrow band for concentrated seal compression
- Requires only one installation tool for all clamp sizes
- Tamper-evident design



Standard PEX Clamp Series vs. PEXGrip® Clamp series

### PEXGrip® Series

- New PEXGrip® Technology\*
- Preset to grip tube
- Prevents clamp from sliding for easier crimping
- Provides a 360° leak-free seal
- Narrow band for concentrated seal compression
- Requires only one installation tool for all clamp sizes
- Tamper-evident design

\*Patent Pending



PEXGrip® Clamp Technology is available in all popular PEX tube sizes

## ORDER INFORMATION

Stepless® Ear Clamps 167 for PEX  
 ASTM F2098 for use with ASTM F1807 and F2159 insert fittings and ASTM F876 PEX tubing.


Clamp size	PEX tube (inch)	Band width x thickness	Standard PEX clamp item no.	PEXGrip® clamp item no.
13.3 mm	3/8"	7.0 x 0.6 mm	16703334	-
17.5 mm	1/2"	7.0 x 0.8 mm	16703335	16707872
20.8 mm	5/8"	7.0 x 0.8 mm	16705571	-
23.3 mm	3/4"	9.0 x 0.8 mm	16703336	16707955
29.6 mm	1"	10.0 x 1.0 mm	16704150	16708152

## PEX | INSTALLATION AND TOOLS


### Installation

For proper installation of clamps, use calibrated genuine Oetiker installation tools.


Learn more  
[www.pex.technology](http://www.pex.technology)



1. Slip clamp over tubing. The recommended distance (dimension) between the "Clamp" and "End of the Tube" is 1/8" – 1/4".



2. Close clamp ear with tool, tool will not release until clamp is fully closed.



3. **IMPORTANT:** For proper installation of Oetiker PEX Series clamps, full ear closure is required. Visually inspect clamp for correct closed ear form.

## HAND INSTALLATION PINCERS (HIP) FOR OETIKER PEX CLAMPS



### 3-Handle Ratchet Pincers

Oetiker 7000 | 280  
 Item no. 14100280

- Single handed installation
- Can be calibrated, with GO/NO-GO gauge included
- Heavy-duty professional grade tool
- Lightweight for easy handling



### DIY Economy 2-Handle Ratchet Pincers

Oetiker 7000 | 337  
 Item no. 14100337

- Light-duty tool
- Includes GO/NO-GO gauge
- Cannot be calibrated, must be disposed
- Lightweight for easy handling

## PNEUMATIC AND CORDLESS PINCERS



### Pneumatic Pincers

Oetiker HO ME 5000/7000

- Installation tool with high process reliability
- High-quality, complete pincer system for uniform clamp closures



### Cordless Pincers

For Ear Clamps  
 Oetiker Cordless Pincer CP 20

- Efficient, uniform and repeatable assembly
- Lightweight, ergonomic design

## ACCESSORIES - CUTTERS



### Hand Clamp Cutter

Oetiker HCC 2000 | 407  
 Item no. 14100407

- Quick and easy ear clamp cutting
- Safest method of clamp removal
- Requires minimal hand force for 1/2" PEX Clamps



### Hand Tubing Cutter

Oetiker HTC 500 | 408  
 Item no. 14100408

- Quickly cuts poly tubing up to 7/8" OD
- V-shaped notch keeps pipe or tube steady
- Light and durable glass filled nylon construction
- Super sharp blade for quick and easy cuts



### Radial Hand Tubing Cutter for PEX Pipe

Oetiker HTC 500 | 418  
 Item no. 14100418

- For PEX tube, plastic conduit and gas pipe
- Cuts 1/2", 3/4" & 1" PEX tube, PEX A, B & C
- Compact tool cuts pipe square, keeps it round
- Straight, circular cuts form tighter connections

**United States:** Oetiker, Inc. | 6317 Euclid Street  
 Marlette, Michigan 48453 | T +1 800 959 0398  
[Info.us.marlette@oetiker.com](mailto:Info.us.marlette@oetiker.com)

[www.pex.technology](http://www.pex.technology)

**Canada:** Oetiker Limited | 203 Dufferin Street South  
 Alliston, Ontario L9R 1W7 | T +1 705 435 4394  
[Info.ca.alliston@oetiker.com](mailto:Info.ca.alliston@oetiker.com)

[www.oetiker.com](http://www.oetiker.com)